



## Double your inlets

The Multi-port kit allows you to increase the amount of inlet ports into your SEP Unit.

### Benefits:

- Space saving - no need for multiple units
- Connect multiple devices to one SEP unit
- Easy to install in situ



## Multi-port Kit

For use with SEP 120, SEP 360, SEP 900 & SEP 1250

## STANDARD SEP Unit

up to 4 inlet ports



All standard single SEP units are shipped with one porting block (as shown) allowing up to 4 inlet pipes to be attached.

Doubling the inlet capacity couldn't be easier with the Multi-port kit:

- 1 Remove the Elbow fitting

## WITH Multi-port Kit

up to 8 inlet ports\*



- 2 Connect the T-Piece in the place of the Elbow.
- 3 Screw fix the second Porting Block.
- 4 Fit the Straight adaptor and Black Tube.



Then simply attach up to four more pipes as you would normally.

**NOTE:** The amount of available inlet ports will depend on the siting of the SEP unit.

\*Maximum of 8 inlet ports is based on the unit being free standing and both port blocks being accessible.

Multi-port kit **CANNOT** be used in conjunction with Wall Mounted Units using the SEPURA™ WMB

For information on the correct positioning and installation of your SEPURA™ Separator Unit please see the accompanying leaflet.



t: +44 (0)1543 379212

e: [sales@sepura-technologies.com](mailto:sales@sepura-technologies.com)

[www.sepura-technologies.com](http://www.sepura-technologies.com)